

HDC SHIELD CLAMP 9.0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Many demands are made on a connector's shielding. Several tailored solutions are available for meeting these requirements:

- A shield discharge via an EMC cable gland
- The use of shield Lever together with shield clamps

Depending on the model, the shield Lever can be used with:

- standard contact inserts
- the ConCept modular system with plastic frame
- the ConCept modular system with metal frame.</>

The shielded conductor is fastened to the shield Lever with shield clamps. The shield clamps are available in various sizes for different sized conductors. .

General ordering data

| | |
|------------|-------------------------------------------------|
| Version | Heavy-duty connectors, Accessories, Shield clip |
| Order No. | 1912240000 |
| Type | HDC SHIELD CLAMP 9.0 |
| GTIN (EAN) | 4032248541560 |
| Qty. | 100 pc(s). |

HDC SHIELD CLAMP 9.0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | |
|------------|--------|
| Net weight | 4.23 g |
|------------|--------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC002943 | ETIM 7.0 | EC002943 |
| ETIM 8.0 | EC002943 | ETIM 9.0 | EC002943 |
| ECLASS 9.0 | 27-44-02-92 | ECLASS 9.1 | 27-44-01-92 |
| ECLASS 10.0 | 27-44-02-92 | ECLASS 11.0 | 27-44-02-92 |
| ECLASS 12.0 | 27-44-02-92 | ECLASS 13.0 | 27-44-02-92 |

Environmental Product Compliance

| | |
|------------|---|
| REACH SVHC | / |
|------------|---|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------------------------------------------------|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | FL FIELDWIRING EN FL FIELDWIRING EN |