

THM MULTIMARK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|---|
| Version | Marking systems, Thermotransfer printer, Thermal transfer, 300 DPI, MultiMark, Shrink-fit sleeves, Label reel |
| Order No. | 2599430000 |
| Type | THM MULTIMARK |
| GTIN (EAN) | 4050118626377 |
| Qty. | 1 pc(s). |

THM MULTIMARK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 253 mm | Depth (inches) | 9.961 inch |
| Height | 320 mm | Height (inches) | 12.598 inch |
| Width | 253 mm | Width (inches) | 9.961 inch |
| Net weight | 5,800 g | | |

Labelling systems

| | | | |
|------------------------|---|---------------------------------------|-------------------|
| Included in delivery | THM MultiMark, Manual, USB cable, Mains cable, Euro plug, US plug, UK plug, Printer driver, Software M-Print® PRO, RIBBON MM-TB 25/360 SW ink ribbon, RIBBON MM 110/360 SW ink ribbon, Ink ribbon core, Print roller, Pressure roller | Interface | USB 2.0, Ethernet |
| Marker type | MultiMark, Shrink-fit sleeves, Label reel | Memory (RAM) | 256 MB |
| Operating system | Windows 7, Windows 8, Windows 8.1, Windows 10 | Operation with rechargeable batteries | No |
| Print resolution, max. | 300 DPI | Printing method | Thermal transfer |
| Printing speed | max. 150 mm/s | Software | M-Print® PRO |
| System requirements | PC with operating system Windows 7, 8 or 10 | Voltage supply | 100...240 V AC |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000610 | ETIM 7.0 | EC000610 |
| ETIM 8.0 | EC000610 | ETIM 9.0 | EC000610 |
| ECLASS 9.0 | 24-32-11-90 | ECLASS 9.1 | 24-32-11-02 |
| ECLASS 10.0 | 24-32-11-90 | ECLASS 11.0 | 24-32-11-90 |
| ECLASS 12.0 | 24-32-11-90 | ECLASS 13.0 | 24-32-11-90 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 7d9d08e1-8ede-49b5-a637-5ea27a383bef |

Approvals

Approvals



ROHS Conform

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | China RoHS Declaration Declaration of Conformity |
| User Documentation | THM MULTIMARK |
| Catalogues | Catalogues in PDF-format |

THM MULTIMARK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Ink ribbons



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|-----------------------------|------------|
| Type | RIBBON MM-HS 60/300 SW | Version |
| Order No. | 2448880000 | Ink ribbon |
| GTIN (EAN) | 4050118462944 | |
| Qty. | 1 pc(s). | |
| Type | RIBBON MM 110/360 SW | Version |
| Order No. | 2005070000 | Ink ribbon |
| GTIN (EAN) | 4050118390049 | |
| Qty. | 1 pc(s). | |
| Type | RIBBON MM 76/360 SW | Version |
| Order No. | 2005080000 | Ink ribbon |
| GTIN (EAN) | 4050118389951 | |
| Qty. | 1 pc(s). | |
| Type | RIBBON MM 84/300 WS | Version |
| Order No. | 2005040000 | Ink ribbon |
| GTIN (EAN) | 4050118390025 | |
| Qty. | 1 pc(s). | |
| Type | RIBBON MM-TB 25/360 SW | Version |
| Order No. | 2005090000 | Ink ribbon |
| GTIN (EAN) | 4050118390216 | |
| Qty. | 1 pc(s). | |
| Type | RIBBON HSS HF EL 40/300 ... | Version |
| Order No. | 1426210000 | Ink ribbon |
| GTIN (EAN) | 4050118228823 | |
| Qty. | 1 pc(s). | |

THM MULTIMARK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

THM MULTIMARK



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | | |
|------------|----------------------------|-------------|
| Type | THM MMP ROLLER MF-W | |
| Order No. | 2519150000 | |
| GTIN (EAN) | 4050118531091 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP ROLLER SFM 2 | |
| Order No. | 2786210000 | |
| GTIN (EAN) | 4064675063230 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP ROLLER TB | |
| Order No. | 2438500000 | |
| GTIN (EAN) | 4050118498721 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP ROLLER 115 | |
| Order No. | 1357420000 | |
| GTIN (EAN) | 4050118160314 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP ROLLER SFM 3 | |
| Order No. | 2719270000 | |
| GTIN (EAN) | 4050118849158 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP EXT.RH | |
| Order No. | 1302920000 | |
| GTIN (EAN) | 4050118102307 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP PERFORATOR | Version |
| Order No. | 1416330000 | Cutting kit |
| GTIN (EAN) | 4050118219388 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP ROLLER MF | |
| Order No. | 2518600000 | |
| GTIN (EAN) | 4050118531305 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP ROLLER SFM 1 | |
| Order No. | 2799000000 | |
| GTIN (EAN) | 4064675259985 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP CUTTER | Version |
| Order No. | 1331600000 | Cutting kit |
| GTIN (EAN) | 4050118163155 | |
| Qty. | 1 pc(s). | |

Creation date July 2, 2024 10:13:31 PM CEST

THM MULTIMARK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories**

| | | |
|------------|----------------------------|------------------|
| Type | THM MMP CASE | Version |
| Order No. | 2457760000 | Empty box / Case |
| GTIN (EAN) | 4050118473131 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP ROLLER SFM 4 | |
| Order No. | 2835010000 | |
| GTIN (EAN) | 4064675427346 | |
| Qty. | 1 pc(s). | |
| Type | THM MMP ROLLER 30 | |
| Order No. | 1357430000 | |
| GTIN (EAN) | 4050118160253 | |
| Qty. | 1 pc(s). | |